


## Instruction for DALI DIMMER 50mA

Model : MD05


- DALI DIMMER 50mA
- Up to 25 DALI ECG by one active DALI DIMMER
- Up to 4 DALI Dimmers can be connected in parallel to set up multiple control points
- Length of the DALI control cable: up to 300 m
- Intuitive manual dimming and switching
- Individual setting of minimal brightness level



### Specification:

Input	Operating voltage	220-240V AC ,50-60 Hz
	No-load consumption	1.0W
Connection	Mains connection	Input: Screw terminal block L, N, Screw terminal block DA+ DA-
	Dali Connection	Max .300m control wire length Max.25 DALI ECG (50mA)
	Allowed leads diameter	0.75 - 3.0mm <sup>2</sup>
Working mode	Press	ON/OFF
	Rotate	Brightness
	Dimming Range	0%-100%
	Ambient temperature	-0°C~50°C
Dimension	Mounting Plate	84*84mm( L*W)
	Recessed installation part	55.4*31mm( Φ*H)
Environment	(Tc)	65°C
	IP Rating	IP20
	Life-time	50,000h

### Dimension



### Operation

- Switch the lighting On/off
- Make a short push onto the rotary knob
- Increase brightness of the lighting
- Turn the rotary knob to the right
- Decrease the brightness of the lighting
- Turn the rotary knob to the left
- Store a fixed switch on level
- Switch on the lighting and adjust brightness level as desired
- Push the knob briefly two times ( double click)
- Storage of the switch on level is confirmed by a two times blinking
- Delete the fixed switch on level
- Switch off the lighting
- Push the knob briefly two times ( double click)
- Deletion of the switch on level is confirmed by a switch on to 100%.

### Areas of application

- Conference rooms
- Restaurants
- Shop lighting

### Wiring :

